

Data sheet

27112.1 PAP 10/2A GN



End plate, Width: 1.5 mm, Colour: Green

Business data

Article number	<u>27112.1</u>
Article name	PAP 10/2A GN
GTIN (EAN)	4044211224851
Packaging unit	20
Quantity unit	PC
Unit of weight	G
Customs number	85389099
Country of origin	DE
Prio-Article	27112.6
Product description	End plate

Data sheet

27112.1 PAP 10/2A GN



Technical data

Dimensions

Length	67.8 mm
Width	1.5 mm
Height	41.5 mm

Materials

Material	Polyamide 6.6
Flammability class UL 94	V-0
Working temperature, min.	-40 °C
Working temperature, max.	120 °C


Environmental Product Compliance

REACH Conform	Yes
REACH Candidate Substance Note	No

Media


Accessories

Terminal blocks



Protective earth terminal, Push-in connection, Mounting type: Mounting rail TS 35/7.5,
Rated cross-section: 10 mm², Width: 10.1 mm, Colour: Green-yellow


Article number	Article name	GTIN (EAN)	Packaging unit
<u>27025.2</u>	PSL 10/2A GNYE	4044211224042	50 ST



Feed-through terminal, Push-in connection, Mounting type: Mounting rail TS 35/7.5,
Rated cross-section: 10 mm², Width: 10.1 mm, Colour: Grey


Article number	Article name	GTIN (EAN)	Packaging unit
<u>27024.6</u>	PRK 10/2A GR	4044211224035	50

##INVERSE##CONTA-CONNECT



Protective earth terminal, Push-in connection, Mounting type: Mounting rail TS 35/7.5,
Rated cross-section: 10 mm², Width: 10.1 mm, Colour: Green-yellow

Article number	Article name	GTIN (EAN)	Packaging unit
<u>27025.2</u>	PSL 10/2A GNYE	4044211224042	50 ST



Feed-through terminal, Push-in connection, Mounting type: Mounting rail TS 35/7.5,
Rated cross-section: 10 mm², Width: 10.1 mm, Colour: Grey

Article number	Article name	GTIN (EAN)	Packaging unit
<u>27024.6</u>	PRK 10/2A GR	4044211224035	50