



Extruded profile for locking base system, length: 2000 mm, lower part, width: 46.5 mm, width of PCB: 42.5 mm, colour: orange, Note: required profile length = PCB length - 4 mm

Business data

Article number	5675.3
Article name	RS-SP 0 2000 mm OG
GTIN (EAN)	4044211068615
Packaging unit	1
Quantity unit	M
Weight per piece (not including packaging)	213 g
Weight per piece (including packaging)	213 g
Unit of weight	G
Customs number	39162000
Country of origin	DE
Product description	Extruded profile
Colour	Orange

Technical data

Dimensions

Length	2000 mm
Width	46.5 mm
Height	19 mm

Materials

Material	PVC
Flammability class UL 94	V-0
Working temperature, min.	-50 °C
Working temperature, max.	60 °C

Further technical data

Required profile length = PCB length	-4 mm
Min. PCB thickness	1.3 mm
Max. PCB thickness	1.7 mm
Min. PCB width of upper level	42.5 mm
Max. PCB width of upper level	42.5 mm

Environmental Product Compliance

REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes

Media

Accessories

Mounting screw



Mounting screw for locking base systems RS-SP, for attaching the mounting feet, end plates and covers

Article number	Article name	GTIN (EAN)	Packaging unit
4560.0	BS RS	4044211080686	100 ST

End plate



End plate with snap-in mounting foot for locking base system RS-SP 0, colour: orange. Enables profile to be mounted on Mounting rail TS 35 DIN rail, colour: orange

Article number	Article name	GTIN (EAN)	Packaging unit
3133.3	AP 0/TS OG	4044211058388	20 ST



Mounting plate for direct mount to locking base system RS-SP 0. Enables profile to be mounted on mounting plates using M5 screw, colour: orange

Article number	Article name	GTIN (EAN)	Packaging unit
3134.3	AP 0/D OG	4044211058395	20 ST