

17272.4 SST/SSIK/LED 30-60V AC/DC



Status display, Display: LED, Mounting type: Plug in, Colour: Black

RAL: 9005

Business data

Article number	17272.4
Article name	SST/SSIK/LED 30-60V AC/DC
GTIN (EAN)	4044211180409
Packaging unit	10
Quantity unit	PC
Weight per piece (not including packaging)	1.86 g
Weight per piece (including packaging)	1.96 g
Unit of weight	G
Customs number	85389099
Country of origin	DE
Product description	Status display
Colour	Black

17272.4 SST/SSIK/LED 30-60V AC/DC

Technical data

Dimensions

Length	30 mm
Width	6.1 mm
Height	14 mm

Connection data

Connection principle	Plug in
----------------------	---------

Materials

Insulation housing	Polyamide 6.6
Flammability class UL 94	V-0
Working temperature, min.	-40 °C
Working temperature, max.	140 °C

Further technical data

Mounting type	Plug in
Fuse size	6,3 x 25 / 6,3 x 32 mm
Voltage illuminated display	30-60 V
Cross-current via illuminated display	< 5 mA
Type of display element (defect display)	LED
Version of fuse cartridge	G fuse 6.3 x 25 / 6.3 x 32
Supply voltage (defect display), min.	30
Supply voltage (defect display), max.	60
Type of voltage (defect display)	AC/DC

Environmental Product Compliance

REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes

Approvals

KEMA KEUR approval

KEMA KEUR approval	EN 60947-7-3:2009
KEMA KEUR approval granted	yes
KEMA rated voltage	60 V

Media



Accessories
