

17274.4 SST/SSIK/LED 500V AC/DC



Status display, Display: LED, Mounting type: Plug in, Colour: Black

RAL: 9005

Business data

Article number	17274.4
Article name	SST/SSIK/LED 500V AC/DC
GTIN (EAN)	4044211180423
Packaging unit	10
Quantity unit	PC
Weight per piece (not including packaging)	1.86 g
Weight per piece (including packaging)	1.96 g
Unit of weight	G
Customs number	85389099
Country of origin	DE
Product description	Status display
Colour	Black

Technical data

Dimensions

Length	30 mm
Width	6.1 mm
Height	14 mm

Connection data

Connection principle	Plug in
----------------------	---------

Materials

Insulation housing	Polyamide 6.6
Flammability class UL 94	V-0
Working temperature, min.	-40 °C
Working temperature, max.	140 °C

Further technical data

Mounting type	Plug in
Fuse size	6,3 x 25 / 6,3 x 32 mm
Voltage illuminated display	500 V
Cross-current via illuminated display	< 5 mA
Type of display element (defect display)	LED
Version of fuse cartridge	G fuse 6.3 x 25 / 6.3 x 32
Supply voltage (defect display), min.	500
Supply voltage (defect display), max.	500
Type of voltage (defect display)	AC/DC

Environmental Product Compliance

REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes

Approvals

KEMA KEUR approval

KEMA KEUR approval	EN 60947-7-3:2009
KEMA KEUR approval granted	yes
KEMA rated voltage	500 V

Media



Accessories
