

# Data sheet

## 27119.3 PAPIKD 2,5 OG



End plate, Width: 1.5 mm, Colour: Orange

### Business data

|                                            |               |
|--------------------------------------------|---------------|
| Article number                             | 27119.3       |
| Article name                               | PAPIKD 2,5 OG |
| GTIN (EAN)                                 | 4044211227326 |
| Packaging unit                             | 20            |
| Quantity unit                              | PC            |
| Weight per piece (not including packaging) | 5.2 g         |
| Weight per piece (including packaging)     | 5.4 g         |
| Unit of weight                             | G             |
| Customs number                             | 85389099      |
| Country of origin                          | DE            |
| Prio-Article                               | 27119.6       |
| Product description                        | End plate     |

---

### Technical data

---

#### Dimensions

|        |         |
|--------|---------|
| Length | 102 mm  |
| Width  | 1.5 mm  |
| Height | 56.2 mm |

#### Materials

|                           |               |
|---------------------------|---------------|
| Material                  | Polyamide 6.6 |
| Flammability class UL 94  | V-0           |
| Working temperature, min. | -40 °C        |
| Working temperature, max. | 120 °C        |

#### Environmental Product Compliance

|                                |    |
|--------------------------------|----|
| REACH Candidate Substance Note | No |
|--------------------------------|----|


---

**Media**

---


Accessories

##INVERSE##CONTA-CONNECT



Three-level initiator terminal | Multi-wire terminal, Push-in connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 2.5 mm², Width: 5,1 mm, Colour: Grey


| Article number | Article name | GTIN (EAN)    | Packaging unit |
|----------------|--------------|---------------|----------------|
| <u>27039.6</u> | PIKD 2,5 GR  | 4044211227210 | 50             |



Three-level initiator terminal | Multi-wire terminal, Push-in connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 2.5 mm², Width: 5.1 mm, Colour: Grey

| Article number | Article name   | GTIN (EAN)    | Packaging unit |
|----------------|----------------|---------------|----------------|
| <u>27041.6</u> | PIKD 2,5/SV GR | 4044211227241 | 50             |

##INVERSE##CONTA-CONNECT



Three-level initiator terminal | Multi-wire terminal, Push-in connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 2.5 mm², Width: 5.1 mm, Colour: Grey

| Article number | Article name   | GTIN (EAN)    | Packaging unit |
|----------------|----------------|---------------|----------------|
| <u>27041.6</u> | PIKD 2,5/SV GR | 4044211227241 | 50             |