


Data sheet

27109.3 PAP 6/2A OG



End plate, Width: 1.5 mm, Colour: Orange

Business data

Article number	27109.3
Article name	PAP 6/2A OG
GTIN (EAN)	4044211224721
Packaging unit	20
Quantity unit	PC
Weight per piece (not including packaging)	2.4 g
Weight per piece (including packaging)	2.6 g
Unit of weight	G
Customs number	85389099
Country of origin	DE
Prio-Article	27109.6
Product description	End plate

Data sheet

27109.3 PAP 6/2A OG



Technical data

Dimensions

Length	57.7 mm
Width	1.5 mm
Height	36 mm


Materials

Material	Polyamide 6.6
Flammability class UL 94	V-0
Working temperature, min.	-40 °C
Working temperature, max.	120 °C

Environmental Product Compliance


REACH Conform	Yes
REACH Candidate Substance Note	No

Media




Accessories

Terminal blocks



Protective earth terminal, Push-in connection, Mounting type: Mounting rail TS 35/7.5,
Rated cross-section: 6 mm², Width: 8.1 mm, Colour: Green-yellow

Article number	Article name	GTIN (EAN)	Packaging unit
<u>27019.2</u>	PSL 6/2A GNYE	4044211223922	50 ST



Feed-through terminal, Push-in connection, Mounting type: Mounting rail TS 35/7.5,
Rated cross-section: 6 mm², Width: 8.1 mm, Colour: Grey


Article number	Article name	GTIN (EAN)	Packaging unit
<u>27018.6</u>	PRK 6/2A GR	4044211223915	50

##INVERSE##CONTA-CONNECT



Protective earth terminal, Push-in connection, Mounting type: Mounting rail TS 35/7.5,
Rated cross-section: 6 mm², Width: 8.1 mm, Colour: Green-yellow

Article number	Article name	GTIN (EAN)	Packaging unit
<u>27019.2</u>	PSL 6/2A GNYE	4044211223922	50 ST



Feed-through terminal, Push-in connection, Mounting type: Mounting rail TS 35/7.5,
Rated cross-section: 6 mm², Width: 8.1 mm, Colour: Grey

Article number	Article name	GTIN (EAN)	Packaging unit
<u>27018.6</u>	PRK 6/2A GR	4044211223915	50