

Partition plate, Width: 1.5 mm, Colour: Beige

Business data

Article number	2105.2
Article name	TW 16 BG
GTIN (EAN)	4044211049195
Packaging unit	20
Quantity unit	PC
Weight per piece (not including packaging)	6.03 g
Weight per piece (including packaging)	6.1 g
Unit of weight	G
Customs number	85389099
Country of origin	DE
Prio-Article	2105.2
Product description	Partition plate

Data sheet

2105.2 TW 16 BG

Technical data

Dimensions

Length	58.7 mm
Width	1.5 mm
Min. thickness	1.5 mm
Height	61.8 mm

Materials

Material	Polyamide 6.6
Flammability class UL 94	V-2
Working temperature, min.	-40 °C
Working temperature, max.	105 °C

Further technical data

Designed as end plate	✓
Snap-on available	✓


Environmental Product Compliance

REACH Candidate Substance Note	No
--------------------------------	----

Media


Accessories

##INVERSE##CONTA-CONNECT




Feed-through terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 16 mm², Width: 12 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1050.2</u>	RK 16 BG	4044211010522	50




Feed-through terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 16 mm², Width: 12 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1162.2</u>	RK 16/Z BG	4044211023607	50



Feed-through terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 16 mm², Width: 12 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1492.2</u>	RK 16/IS BG	4044211045234	50



Feed-through terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 16 mm², Width: 12 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1493.2</u>	RK 16/Z/IS BG	4044211045258	50