

# Data sheet

## 2490.1 K 35 GNYE



Cap, Colour: Green-yellow

### Business data

Article number	2490.1
Article name	K 35 GNYE
GTIN (EAN)	4044211052881
Packaging unit	50
Quantity unit	PC
Weight per piece (not including packaging)	1.08 g
Weight per piece (including packaging)	1.1 g
Unit of weight	G
Customs number	85389099
Country of origin	DE
Prio-Article	2490.1
Product description	Cap

# Data sheet

## 2490.1 K 35 GNYE



---

### Technical data

---

#### Materials

Material	Polyamide 6.6
Flammability class UL 94	V-2
Working temperature, min.	-40 °C
Working temperature, max.	105 °C

#### Further technical data

Mounting type	Plug in
---------------	---------

#### Environmental Product Compliance

REACH Candidate Substance Note	No
--------------------------------	----

---

**Media**

---

### Accessories

#### Terminal blocks



Clamping yoke, Screw connection, Mounting type: Can be screwed on, Rated cross-section: 35 mm², Colour: Green-yellow

Article number	Article name	GTIN (EAN)	Packaging unit
<u>2485.1</u>	ZB 35/K GNYE	4044211052775	20

#### ##INVERSE##CONTA-CONNECT



Clamping yoke, Screw connection, Mounting type: Can be screwed on, Rated cross-section: 35 mm², Colour: natural

Article number	Article name	GTIN (EAN)	Packaging unit
<u>2305.0</u>	ZB 35	4044211050924	20 ST



Clamping yoke, Screw connection, Mounting type: Can be screwed on, Rated cross-section: 35 mm², Colour: Green-yellow

Article number	Article name	GTIN (EAN)	Packaging unit
<u>2485.1</u>	ZB 35/K GNYE	4044211052775	20