

Data sheet

2574.1 AP 2,5-4/R GN



End plate, Width: 1.5 mm, Colour: Green

Business data

Article number	2574.1
Article name	AP 2,5-4/R GN
GTIN (EAN)	4044211053642
Packaging unit	50
Quantity unit	PC
Weight per piece (not including packaging)	2.65 g
Weight per piece (including packaging)	2.68 g
Unit of weight	G
Customs number	85389099
Country of origin	DE
Prio-Article	2574.2
Product description	End plate

Technical data

Dimensions

Length	57.5 mm
Width	1.5 mm
Min. thickness	1.5 mm
Height	31.5 mm

Materials

Material	Polyamide 6.6
Flammability class UL 94	V-2
Working temperature, min.	-40 °C
Working temperature, max.	105 °C

Further technical data

Designed as end plate	✓
Snap-on available	✓


Environmental Product Compliance

REACH Candidate Substance Note	No
--------------------------------	----

Media


Accessories

##INVERSE##CONTA-CONNECT



Protective earth terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5,
Rated cross-section: 2.5 mm², Width: 6 mm, Colour: Green-yellow

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1060.2</u>	SL 2,5/35/ZR GNYE	4044211011727	100 ST



Feed-through terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32,
Rated cross-section: 4 mm², Width: 6 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1210.2</u>	RK 2,5-4/ZR BG	4044211028459	100