


Data sheet

3758.1 ZAP SR/RC GN



End plate, Width: 5.1 mm, Colour: Green

Business data

Article number	3758.1
Article name	ZAP SR/RC GN
GTIN (EAN)	4044211060732
Packaging unit	50
Quantity unit	PC
Weight per piece (not including packaging)	2.2 g
Weight per piece (including packaging)	2.3 g
Unit of weight	G
Customs number	85389099
Country of origin	DE
Prio-Article	3758.2
Product description	End plate

Technical data

Dimensions

Length	40 mm
Width	5.1 mm
Height	23.9 mm

Materials

Material	Polyamide 6.6
Flammability class UL 94	V-2
Working temperature, min.	-40 °C
Working temperature, max.	105 °C

Further technical data

Designed as end plate	✓
Snap-on available	✓

Environmental Product Compliance

REACH Conform	Yes
REACH Candidate Substance Note	No

Media

Accessories

##INVERSE##CONTA-CONNECT



Ex feed-through terminal for direct mount, ATEX-certified, Tension-spring connection, Mounting type: Mounting surface, Rated cross-section: 25 mm², Width: 51 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1729.2</u>	ZSRK 2,5/2A-D Ex BG	4044211129699	100 ST



Feed-through terminal for direct mount, Tension-spring connection, Mounting type: Mounting surface, Rated cross-section: 2.5 mm², Width: 5.1 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>3588.2</u>	ZSRK 2,5/2A-D BG	4044211151966	100



Feed-through terminal for direct mount, Tension-spring connection, Mounting type: Mounting surface, Rated cross-section: 2.5 mm², Width: 5.1 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>3587.2</u>	ZSRK 2,5/2A-RC BG	4044211151942	100

##INVERSE##CONTA-CONNECT