

Data sheet

17268.2 ADH 70 BG



Cover profile, Length: 86.8 mm, Width: 31.9 mm, Colour: Beige

Business data

Article number	17268.2
Article name	ADH 70 BG
GTIN (EAN)	4044211186876
Packaging unit	10
Quantity unit	PC
Weight per piece (not including packaging)	10 g
Weight per piece (including packaging)	10.4 g
Unit of weight	G
Customs number	85389099
Country of origin	DE
Prio-Article	17268.8
Product description	Cover profile

Data sheet

17268.2 ADH 70 BG



Technical data

Dimensions

Length	86.8 mm
Width	31.9 mm
Height	33.7 mm

Materials

Material	Polyamide 6.6
Flammability class UL 94	V-0
Working temperature, min.	-40 °C
Working temperature, max.	120 °C


Environmental Product Compliance

REACH Candidate Substance Note	No
--------------------------------	----

Media

Accessories

##INVERSE##CONTA-CONNECT



High-power stud terminal, Stud connection, Mounting type: Mounting rail TS 35/7.5,
Rated cross-section: 70 mm², Width: 32 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>17035.2</u>	HSKG 70/M8/B/B BG	4044211186593	10 ST