

Data sheet

17432.6 SDK 4-FP GR



Flange plate, Colour: Grey

RAL: 7032

Business data

Article number	<u>17432.6</u>
Article name	SDK 4-FP GR
GTIN (EAN)	4044211199265
Packaging unit	50
Quantity unit	PC
Weight per piece (not including packaging)	2.8 g
Weight per piece (including packaging)	2.9 g
Unit of weight	G
Customs number	85389099
Country of origin	DE
Product description	Flange plate
Colour	Grey

Data sheet

17432.6 SDK 4-FP GR



Technical data

Dimensions

Length	63.2 mm
Width	10.75 mm
Height	27.5 mm

Materials

Material	Polyamide 6.6
Flammability class UL 94	V-0
Working temperature, min.	-40 °C
Working temperature, max.	120 °C

Environmental Product Compliance

REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes

Media

Accessories

##INVERSE##CONTA-CON



Feed-through terminal, Screw connection, Mounting type: Mounting surface, Rated cross-section: 4 mm², Colour: Grey

Article number	Article name	GTIN (EAN)	Packaging unit
<u>17380.6</u>	SDK 4/2A GR	4044211199227	50 ST



Feed-through terminal, Screw connection, Mounting type: Mounting surface, Rated cross-section: 4 mm², Colour: Grey

Article number	Article name	GTIN (EAN)	Packaging unit
<u>17381.6</u>	SDK 4/2A/Z GR	4044211199234	50 ST



Feed-through terminal, Screw connection, Mounting type: Mounting surface, Rated cross-section: 4 mm², Colour: Grey

Article number	Article name	GTIN (EAN)	Packaging unit
<u>17382.6</u>	SDK 4/1A/1L GR	4044211199241	50 ST



Feed-through terminal, Screw connection, Mounting type: Mounting surface, Rated cross-section: 4 mm², Colour: Grey

Article number	Article name	GTIN (EAN)	Packaging unit
<u>17383.6</u>	SDK 4/1A/1L/Z GR	4044211206277	50 ST