

# Product data sheet

## Characteristics

# 9080GC6B

Terminal block, Linergy, end barrier, natural color, for 9080GC6 terminal block



### Main

Range of Product	9080G
Product or Component Type	End Barrier

### Complementary

Material	Nylon
Color	Natural
Package Quantity	Set of 10
Mounting Type	35 mm DIN rail 9080GH track
Height	1.95 in (49.53 mm)
Width	1.99 in (50.55 mm)
Depth	0.12 in (3.05 mm)

### Environment

Ambient Air Temperature for Operation	-40...257 °F (-40...125 °C)
---------------------------------------	-----------------------------

### Ordering and shipping details

Category	21702-9080 G (NOT GCB)
Discount Schedule	CP5
GTIN	785901155010
Nbr. of units in pkg.	1
Package weight(Lbs)	0.16 oz (4.536 g)
Returnability	Yes
Country of origin	MX

### Packing Units

Unit Type of Package 1	PCE
Package 1 Height	4.57 in (11.613 cm)
Package 1 width	1.80 in (4.572 cm)
Package 1 Length	11.61 in (29.497 cm)
Unit Type of Package 2	CAR
Number of Units in Package 2	10

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
PVC free	Yes

## Contractual warranty

Warranty	18 months
----------	-----------