

PS-3,5 - Test plug

3031010

<https://www.phoenixcontact.com/us/products/3031010>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Test plug, Modular test plug, number of positions: 1, color: red

Your advantages

- Test adapters can be assembled individually using PS-... modular test plugs
- The test plugs make contact in the function shaft of terminal blocks from the CLIPLINE complete system

Commercial data

Item number	3031010
Packing unit	10 pc
Sales key	BE29
Product key	BE2Z3X
Catalog page	Page 38 (C-1-2019)
GTIN	4046356728003
Weight per piece (including packing)	1.74 g
Weight per piece (excluding packing)	1.7 g
Customs tariff number	85366990
Country of origin	PL

PS-3,5 - Test plug

3031010

<https://www.phoenixcontact.com/us/products/3031010>



Technical data

Product properties

Product type	Test plug terminal block
Number of positions	1
Potentials	1

Electrical properties

Maximum load current	2 A
Max. voltage	250 V

Connection data

Maximum load current	2 A
Connection method	Push-in connection
Conductor cross section flexible	0.14 mm ² ... 1.5 mm ²

Dimensions

Width	3.5 mm
Height	15.9 mm
Depth	43.3 mm

Material specifications

Color	red
Material	PA
Flammability rating according to UL 94	V0

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

Connection method	Push-in connection
-------------------	--------------------

PS-3,5 - Test plug

3031010

<https://www.phoenixcontact.com/us/products/3031010>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3031010>



EAC

Approval ID: RU C-DE.BL08.B.00511

PS-3,5 - Test plug

3031010

<https://www.phoenixcontact.com/us/products/3031010>



Classifications

ECLASS

ECLASS-11.0	27141148
ECLASS-12.0	27141148
ECLASS-13.0	27250304

ETIM

ETIM 9.0	EC002555
----------	----------

UNSPSC

UNSPSC 21.0	20122000
-------------	----------

PS-3,5 - Test plug



3031010
<https://www.phoenixcontact.com/us/products/3031010>

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com