

Product data sheet

Specifications



Cable ends, Linergy TR cable ends, single conductor, grey, 0.5mm², medium size, 10 sets of 100

DZ5CE042

Main

Range of product	Linergy
Product or component type	Cable end
Cable end size	Medium
Standards	NF C 63-023
Type of packing	String of bags
Quantity per set	10 sets of 100
Cable cross section	4 mm ²

Complementary

Cable end type	Single conductor
Additional information	Without marker tag holder
Colour	Orange
Bezel material	Halogen-free plastic
Tube material	Copper conforming to ISO 1337
Number of cables	1
AWG gauge	AWG 12
Bezel size	Ø 5.4 mm
Tube diameter	3.2 mm
Length	17 mm
Tube length	10 mm
Net weight	0.3 kg

Environment

Product certifications	UL
Ambient air temperature for operation	-20...105 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Package 1 Height	0.400 cm
Package 1 Width	0.400 cm
Package 1 Length	1.400 cm
Package 1 Weight	0.200 g
Unit Type of Package 2	BB1
Number of Units in Package 2	1000
Package 2 Height	5.000 cm
Package 2 Width	12.000 cm
Package 2 Length	26.000 cm
Package 2 Weight	270.000 g
Unit Type of Package 3	S03
Number of Units in Package 3	30000
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	8.613 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
RoHS exemption information	Yes
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)