


Product data sheet

Specifications



Fuse carrier, TeSys DF, 2P, 30A, 600VAC, fuse class CC

DFCC2

Main

Range	TeSys
Product name	TeSys DF
Product or component type	Fuse carrier
Device short name	DFCC
Poles description	2P
Fuse type	, CC
Control type	Toggle padlockable
Utilisation category	AC-20B conforming to IEC 60947-3
[Ue] rated operational voltage	600 V AC
[Ie] rated operational current	30 A
[Ui] rated insulation voltage	600 V AC
[Uimp] rated impulse withstand voltage	6 kV
Short-circuit withstand	200 kA 600 V conforming to UL 512
Power dissipation in W	3 W maximum power dissipation by fuse

Complementary

Standards	UL 4248-1 UL 4248-4 CSA C22.2 No 4248-1 CSA C22.2 No 4248-4
Product certifications	UL recognized CSA
Mounting support	35 mm symmetrical DIN rail
Mounting position	Vertical (tolerance: +/- 23°)
Connections - terminals	Screw clamp terminals 1 cable(s) 1...16 mm²rigid Screw clamp terminals 2 cable(s) 1...6 mm²rigid Screw clamp terminals 1 cable(s) 1...16 mm²flexible with or without Screw clamp terminals 2 cable(s) 1...6 mm²flexible with or without
Tightening torque	2 N.m - with screwdriver PZ2 2 N.m - with screwdriver flat Ø 5.5 mm
Height	79.5 mm
Width	35 mm
Depth	61 mm

Net weight	0.085 kg
Quantity per set	Set of 12
Environment	
Ambient air temperature for storage	-40...70 °C
Ambient air temperature for operation	-40...70 °C with derating above 20°C
Operating altitude	0...2000 m without derating
IP degree of protection	IP20
Pollution degree	3
Fire resistance	960 °C conforming to IEC 60695-2-1
Compatibility code	DFCC
Packing Units	
Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.800 cm
Package 1 Width	3.500 cm
Package 1 Length	6.400 cm
Package 1 Weight	94.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Height	6.800 cm
Package 2 Width	8.500 cm
Package 2 Length	22.200 cm
Package 2 Weight	568.000 g
Unit Type of Package 3	S03
Number of Units in Package 3	96
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	9.598 kg
Offer Sustainability	
Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
RoHS exemption information	Yes

Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
California proposition 65	WARNING: Cancer - www.P65Warnings.ca.gov

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)