

Product data sheet

Specifications



Cable ends, Linergy TR cable ends, single conductor, 10mm², for un-insulated cable, medium size, 10 sets of 100

DZ5CE100

Main

Range of product	Linergy
Product or component type	Cable end
Cable end size	Medium
Standards	DIN 46228-1
Type of packing	Individual bag
Quantity per set	Set of 100
Cable cross section	10 mm ²

Complementary

Cable end type	Single conductor
Additional information	Non-insulated
Bezel material	Halogen-free plastic
Tube material	Copper conforming to ISO 1337
Number of cables	1
AWG gauge	AWG 8
Bezel size	Ø 5.8 mm
Tube diameter	4.5 mm
Length	18 mm
Tube length	18 mm

Environment

Ambient air temperature for operation	-20...105 °C
---------------------------------------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.400 cm
Package 1 Width	0.400 cm
Package 1 Length	1.400 cm

Package 1 Weight	0.100 g
Unit Type of Package 2	BB1
Number of Units in Package 2	100
Package 2 Height	3.000 cm
Package 2 Width	4.500 cm
Package 2 Length	12.500 cm
Package 2 Weight	48.000 g
Unit Type of Package 3	S02
Number of Units in Package 3	7000
Package 3 Height	15.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	3.720 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
RoHS exemption information	Yes
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

Recommended replacement(s)