



Main

Range of Product	Harmony 9001B
Product or Component Type	Complete control station
Device short name	9001BR
Control station application	Two functions
Colour of base of enclosure	Grey

Complementary

Material	Cast zinc
Marking	CE
Type of operator	maintained
Control station composition	1 push-button, black without marking 1 push-button, black
Contacts type and composition	1 NO + 1 NC
Mechanical durability	5000000 cycles
[Ie] rated operational current	5 A 600 V, AC
Device mounting	Surface
Type of Installation	Indoor

Environment

Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Ambient air temperature for operation	-13...158 °F (-25...70 °C)
NEMA degree of protection	NEMA 7/9
Product Certifications	CSA LR25490 class 3211 03 UL listed file E42259 CCN NKCR
Environmental characteristic	Hazardous location

Ordering and shipping details

Category	21421 - 9001 B (NOT BW70 - BW80)
Discount Schedule	CS1
GTIN	785901600916
Nbr. of units in pkg.	1
Package weight(Lbs)	3.69 lb(US) (1.674 kg)
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	13.97 in (35.484 cm)
Package 1 width	5.50 in (13.97 cm)
Package 1 Length	35.48 in (90.129 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------