



Main

Range of Product	Harmony 9001KY
Product or Component Type	Control station
Device short name	9001SK
Level or class	Class III Class II Division 2 Group G

Complementary

Type of Installation	Indoor/outdoor
Connector Type	Screw clamp connector
[Ue] rated operational voltage	600 V
[Ie] rated operational current AC	10 A

Environment

NEMA Degree of Protection	NEMA 1 NEMA 3 NEMA 13 NEMA 4
Environmental characteristic	Dust and oil resistant Resistant against immersion in water
Ambient Air Temperature for Operation	-13...140 °F (-25...60 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)

Ordering and shipping details

Category	21429-9001 SK,SKY
Discount Schedule	CS1
GTIN	785901546733
Nbr. of units in pkg.	1
Package weight(Lbs)	1.76 oz (49.895 g)
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.54 in (6.452 cm)
Package 1 width	1.00 in (2.54 cm)
Package 1 Length	6.45 in (16.387 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------