

Product data sheet

Specifications



Cable ends, Linergy TR cable ends, single conductor, red, 1mm², medium size, 5 sets of 200

AZ5CE010

Main

Range of product	Linergy
Product or component type	Cable end
Cable end size	Medium
Standards	NF C 63-023
Type of packing	Dispenser pack
Quantity per set	5 sets of 200
Cable cross section	1 mm ²

Complementary

Cable end type	Single conductor
Additional information	Without marker tag holder
Colour	Red
Bezel material	Halogen-free plastic
Tube material	Copper conforming to ISO 1337
Number of cables	1
AWG gauge	AWG 18
Bezel size	Ø 3.5 mm
Tube diameter	1.7 mm
Length	14 mm
Tube length	8 mm
Net weight	0.165 kg

Environment

Product certifications	UL
Ambient air temperature for operation	-20...105 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Package 1 Height	0.4 cm
Package 1 Width	0.4 cm
Package 1 Length	1.4 cm
Package 1 Weight	1 g
Unit Type of Package 2	BB1
Number of Units in Package 2	1000
Package 2 Height	13 cm
Package 2 Width	7 cm
Package 2 Length	12.5 cm
Package 2 Weight	1000 g
Unit Type of Package 3	S04
Number of Units in Package 3	40000
Package 3 Height	30 cm
Package 3 Width	40 cm
Package 3 Length	60 cm
Package 3 Weight	40 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
RoHS exemption information	Yes
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)