



Main

Range of Product	Harmony 9001K
Product or Component Type	Security control station
Device short name	9001KY
Lock type	Complete with core, 7 tumbler pins

Complementary

Size	30 mm
Enclosure/cubicle description	Surface mounting
Enclosure Material	Cast Aluminium
Type of Installation	Indoor/outdoor
Control station composition	1 key selector switch, spring return OPEN-CLOSE
Type of Keylock	Best
Key withdrawal position	Center
Connections - terminals	Screw clamp terminal
[Ue] rated operational voltage	300 V
[Ie] rated operational current AC	15 A
Net Weight	3.55 lb(US) (1.61 kg)

Environment

NEMA Degree of Protection	NEMA 3R
Environmental characteristic	Waterproof
Product Certifications	CE UL Listed CSA
Ambient Air Temperature for Operation	-13...140 °F (-25...60 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)

Ordering and shipping details

Category	21426-9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
GTIN	785901347460
Nbr. of units in pkg.	1
Package weight(Lbs)	3.75 lb(US) (1.701 kg)
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	11.43 in (29.032 cm)
Package 1 width	4.50 in (11.43 cm)
Package 1 Length	29.03 in (73.742 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------