

# Product data sheet

Specifications



Cable ends, Linergy TR cable ends, single conductor, grey, 0.75mm<sup>2</sup>, for insulated cable, short size, 10 sets of 100

DZ5CE007L6D

## Main

|                           |                      |
|---------------------------|----------------------|
| Range of product          | Linergy              |
| Product or component type | Cable end            |
| Cable end size            | Short                |
| Standards                 | DIN 46228-4          |
| Type of packing           | String of bags       |
| Quantity per set          | 10 sets of 100       |
| Cable cross section       | 0.75 mm <sup>2</sup> |

## Complementary

|                        |                               |
|------------------------|-------------------------------|
| Cable end type         | Single conductor              |
| Additional information | Without marker tag holder     |
| Colour                 | Grey                          |
| Bezel material         | Halogen-free plastic          |
| Tube material          | Copper conforming to ISO 1337 |
| Number of cables       | 1                             |
| AWG gauge              | AWG 20                        |
| Bezel size             | Ø 3.3 mm                      |
| Tube diameter          | 1.5 mm                        |
| Length                 | 12 mm                         |
| Tube length            | 6 mm                          |
| Net weight             | 0.095 kg                      |

## Environment

|                                       |              |
|---------------------------------------|--------------|
| Product certifications                | UL           |
| Ambient air temperature for operation | -20...105 °C |

## Packing Units

|                              |     |
|------------------------------|-----|
| Unit Type of Package 1       | PCE |
| Number of Units in Package 1 | 1   |

|                              |           |
|------------------------------|-----------|
| Package 1 Height             | 0.400 cm  |
| Package 1 Width              | 0.400 cm  |
| Package 1 Length             | 1.400 cm  |
| Package 1 Weight             | 0.100 g   |
| Unit Type of Package 2       | BB1       |
| Number of Units in Package 2 | 1000      |
| Package 2 Height             | 4.000 cm  |
| Package 2 Width              | 7.000 cm  |
| Package 2 Length             | 10.000 cm |
| Package 2 Weight             | 101.000 g |
| Unit Type of Package 3       | S01       |
| Number of Units in Package 3 | 2000      |
| Package 3 Height             | 15.000 cm |
| Package 3 Width              | 15.000 cm |
| Package 3 Length             | 40.000 cm |
| Package 3 Weight             | 367.000 g |

## Offer Sustainability

|                             |   |
|-----------------------------|---|
| Sustainable offer status    | Green Premium product   |
| REACH Regulation            | <a href="#">REACH Declaration</a>   |
| REACH free of SVHC          | Yes   |
| EU RoHS Directive           | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a>           |
| Toxic heavy metal free      | Yes   |
| Mercury free                | Yes   |
| China RoHS Regulation       | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope) |
| RoHS exemption information  | <a href="#">Yes</a>   |
| Circularity Profile         | No need of specific recycling operations  |
| PVC free                    | Yes   |
| Halogen content performance | Halogen free plastic parts product  |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Recommended replacement(s)