

Product data sheet

Specifications



Cable end, Linergy TR cable ends, single conductor, red, 35mm², long size, for clip-in type, 10 sets of 100

DZ5CA353

Main

| | |
|---------------------------|--------------------|
| Range of product | Linergy |
| Product or component type | Cable end |
| Cable end size | Long |
| Standards | NF C 63-023 |
| Type of packing | Bag |
| Quantity per set | Set of 20 |
| Cable cross section | 35 mm ² |

Complementary

| | |
|------------------------|----------------------------------|
| Cable end type | Single conductor |
| Additional information | For additional marker tag holder |
| Colour | Red |
| Bezel material | Halogen-free plastic |
| Tube material | Copper conforming to ISO 1337 |
| Number of cables | 1 |
| AWG gauge | AWG 2 |
| Bezel size | Ø 13.5 mm |
| Tube diameter | 8.7 mm |
| Length | 39 mm |
| Tube length | 25 mm |
| CAD overall depth | 39 mm |
| Net weight | 0.06 kg |

Environment

| | |
|---------------------------------------|--------------|
| Ambient air temperature for operation | -20...105 °C |
|---------------------------------------|--------------|

Packing Units

| | |
|------------------------------|-----|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |

| | |
|------------------------------|-----------|
| Package 1 Height | 0.400 cm |
| Package 1 Width | 0.400 cm |
| Package 1 Length | 1.400 cm |
| Package 1 Weight | 1.700 g |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 20 |
| Package 2 Height | 3.000 cm |
| Package 2 Width | 6.000 cm |
| Package 2 Length | 12.000 cm |
| Package 2 Weight | 41.000 g |
| Unit Type of Package 3 | S02 |
| Number of Units in Package 3 | 1500 |
| Package 3 Height | 15.000 cm |
| Package 3 Width | 30.000 cm |
| Package 3 Length | 40.000 cm |
| Package 3 Weight | 2.926 kg |

Offer Sustainability

| | |
|-----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| RoHS exemption information | Yes |
| Circularity Profile | No need of specific recycling operations |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| PVC free | Yes |
| Halogen content performance | Halogen free plastic parts product |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Recommended replacement(s)