

# Product data sheet

Specifications



Cable end, Linergy TR cable ends, single conductor, red, 10mm<sup>2</sup>, for insulated cable, medium size, 10 sets of 100

DZ5CA102D

## Main

|                           |                    |
|---------------------------|--------------------|
| Range of product          | Linergy            |
| Product or component type | Cable end          |
| Cable end size            | Medium             |
| Standards                 | DIN 46228-4        |
| Type of packing           | Bag                |
| Quantity per set          | Set of 100         |
| Cable cross section       | 10 mm <sup>2</sup> |

## Complementary

|                        |                                  |
|------------------------|----------------------------------|
| Cable end type         | Single conductor                 |
| Additional information | For additional marker tag holder |
| Colour                 | Red                              |
| Bezel material         | Halogen-free plastic             |
| Tube material          | Copper conforming to ISO 1337    |
| Number of cables       | 1                                |
| AWG gauge              | AWG 8                            |
| Bezel size             | Ø 8.4 mm                         |
| Tube diameter          | 4.9 mm                           |
| Length                 | 22 mm                            |
| Tube length            | 12 mm                            |
| CAD overall depth      | 22 mm                            |
| Net weight             | 0.06 kg                          |

## Environment

|                                       |              |
|---------------------------------------|--------------|
| Ambient air temperature for operation | -20...105 °C |
|---------------------------------------|--------------|

## Packing Units

|                              |     |
|------------------------------|-----|
| Unit Type of Package 1       | PCE |
| Number of Units in Package 1 | 1   |

|                              |           |
|------------------------------|-----------|
| Package 1 Height             | 0.400 cm  |
| Package 1 Width              | 0.400 cm  |
| Package 1 Length             | 1.400 cm  |
| Package 1 Weight             | 0.500 g   |
| Unit Type of Package 2       | BB1       |
| Number of Units in Package 2 | 100       |
| Package 2 Height             | 2.000 cm  |
| Package 2 Width              | 15.000 cm |
| Package 2 Length             | 5.500 cm  |
| Package 2 Weight             | 54.000 g  |
| Unit Type of Package 3       | S01       |
| Number of Units in Package 3 | 3000      |
| Package 3 Height             | 15.000 cm |
| Package 3 Width              | 15.000 cm |
| Package 3 Length             | 40.000 cm |
| Package 3 Weight             | 1.807 kg  |

## Offer Sustainability

|                             |                                                                                                                             |
|-----------------------------|-----------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status    | Green Premium product                                                                                                       |
| REACH Regulation            | <a href="#">REACH Declaration</a>                                                                                           |
| REACH free of SVHC          | Yes                                                                                                                         |
| EU RoHS Directive           | Compliant<br><a href="#">EU RoHS Declaration</a>                                                                            |
| Toxic heavy metal free      | Yes                                                                                                                         |
| Mercury free                | Yes                                                                                                                         |
| China RoHS Regulation       | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope)                 |
| RoHS exemption information  | <a href="#">Yes</a>                                                                                                         |
| Circularity Profile         | No need of specific recycling operations                                                                                    |
| WEEE                        | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| PVC free                    | Yes                                                                                                                         |
| Halogen content performance | Halogen free plastic parts product                                                                                          |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Recommended replacement(s)