

D-PTIO 1,5/S/5 - End cover

3244589

<https://www.phoenixcontact.com/us/products/3244589>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

End cover, depth: 44.6 mm, width: 0.8 mm, height: 121.65 mm, color: gray



Your advantages

- End cover, enables the open terminal side to be covered

Commercial data

Item number	3244589
Packing unit	50 pc
Sales key	BE29
Product key	BE2Z1X
Catalog page	Page 42 (C-1-2019)
GTIN	4055626447896
Weight per piece (including packing)	3.98 g
Weight per piece (excluding packing)	3.87 g
Customs tariff number	85389099
Country of origin	PL

D-PTIO 1,5/S/5 - End cover

3244589

<https://www.phoenixcontact.com/us/products/3244589>



Technical data

Product properties

Product type	End cover
--------------	-----------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Material specifications

Color	gray
Material	PA
Flammability rating according to UL 94	V0
Static insulating material application in cold	-60 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Dimensions

Width	0.8 mm
End cover width	0.8 mm
Height	121.65 mm
Depth	44.6 mm
Depth on NS 35/7,5	52.1 mm
Depth on NS 35/15	59.6 mm

D-PTIO 1,5/S/5 - End cover

3244589

<https://www.phoenixcontact.com/us/products/3244589>



Classifications

ECLASS

ECLASS-11.0	27141133
ECLASS-12.0	27141133
ECLASS-13.0	27250301

ETIM

ETIM 9.0	EC000886
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

D-PTIO 1,5/S/5 - End cover

3244589

<https://www.phoenixcontact.com/us/products/3244589>



Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com