



Crimp lug, Length: 24 mm, Max. wire cross-section: 6 mm², Colour: Yellow

RAL: 1026

Business data

|                                            |               |
|--------------------------------------------|---------------|
| Article number                             | 2560.0        |
| Article name                               | FST 6/6,3     |
| GTIN (EAN)                                 | 4044211053536 |
| Packaging unit                             | 100           |
| Quantity unit                              | PC            |
| Weight per piece (not including packaging) | 1.61 g        |
| Weight per piece (including packaging)     | 1.8 g         |
| Unit of weight                             | G             |
| Customs number                             | 85369010      |
| Country of origin                          | TW            |
| Product description                        | Crimp         |
| Colour                                     | Yellow        |

### Technical data

#### Dimensions

|                            |        |
|----------------------------|--------|
| Length                     | 24 mm  |
| Length of connector        | 8 mm   |
| Plug width                 | 6.3 mm |
| Diameter of feed-in funnel | 6.2 mm |
| Plug thickness             | 0.8 mm |

#### Connection data

|                              |                   |
|------------------------------|-------------------|
| Wire cross-section, min.     | 4 mm <sup>2</sup> |
| Wire cross-section, max.     | 6 mm <sup>2</sup> |
| Wire cross-section AWG, min. | 12                |
| Wire cross-section AWG, max. | 10                |

#### Materials

|                           |                         |
|---------------------------|-------------------------|
| Connector material        | Copper                  |
| Surface                   | Tin-plated              |
| insul.                    | Expanded PVC insulation |
| Working temperature, min. | -10 °C                  |
| Working temperature, max. | 75 °C                   |

#### Further technical data

|                      |   |
|----------------------|---|
| Insulation available | ✓ |
|----------------------|---|

#### Environmental Product Compliance

|                                |            |
|--------------------------------|------------|
| REACH Conform                  | yes        |
| REACH Reference date           | 2023-06-14 |
| REACH Candidate Substance Note | No         |
| RoHS Conform                   | yes        |

---

**Media**

---

---

**Accessories**

---