

ATGBICS EX-SFP-1GE-T-C-C network transceiver module Copper 1000 Mbit/s

Brand : ATGBICS

Product code: EX-SFP-1GE-T-C-C

Product name : EX-SFP-1GE-T-C-C



Juniper Compatible Transceiver SFP 10/100/1000Base-T Copper RJ45 Connector 100m

[ATGBICS EX-SFP-1GE-T-C-C network transceiver module Copper 1000 Mbit/s:](#)

ATGBICS EX-SFP-1GE-T-C SFP operates on standard Category 5 unshielded twisted-pair copper cabling of link lengths up to 100m. Juniper 1000BASE-T SFP modules support 10/100/1000 auto negotiation and auto MDI/MDIX. Our product is built to the exact specification of Juniper EX-SFP-1GE-T-C= and we proudly offer a compatibility guarantee and lifetime warranty. Our rigorously tested products record a unique traceable serial number and are fully compliant with all MSA Standards.

ATGBICS EX-SFP-1GE-T-C-C. SFP transceiver type: Copper, Maximum data transfer rate: 1000 Mbit/s, Interface type: SFP. Product colour: Silver, Housing material: Metal, Country of origin: United Kingdom. Input voltage: 3.3 V, Maximum voltage: 4 V, Power consumption (typical): 1.3 W. Width: 13.4 mm, Depth: 56.5 mm, Height: 8.5 mm. Number of products included: 1 pc(s), Package type: Box



Performance		Features	
SFP transceiver type *	Copper	Brand compatibility	Juniper
Maximum data transfer rate *	1000 Mbit/s	Power	
Interface type *	SFP	Input voltage	3.3 V
Single-mode fiber (SMF) supported	✗	Maximum voltage	4 V
Multi-mode fiber (MMF) supported	✗	Power consumption (typical)	1.3 W
SFP transceiver standard	TX	Operational conditions	
Maximum transfer distance	100 m	Maximum operating temperature	70 °C
Ethernet LAN	✓	Operating temperature (T-T)	0 - 70 °C
Ethernet interface type	Gigabit Ethernet	Storage temperature (T-T)	-40 - 85 °C
Copper ethernet cabling technology	10BASE, 100BASE, 1000BASE	Operating relative humidity (H-H)	5 - 85%
Auto MDI/MDI-X	✓	Storage relative humidity (H-H)	5 - 85%
Digital Diagnostics Monitoring (DDM)	✗	Weight & dimensions	
Features		Width	13.4 mm
Product colour	Silver	Depth	56.5 mm
Housing material	Metal	Height	8.5 mm
Plug and Play	✓	Weight	20 g
Hot-Plug support	✓	Packaging data	
Hot-swap	✓	Number of products included	1 pc(s)
Easy to install	✓	Package type	Box
Country of origin	United Kingdom	Technical details	
		Sustainability certificates	RoHS



5056468700896

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 26-JAN-2024. Prints or copies of Information are only valid on the printed Publication date