

ATGBICS FTLF8532P5BNV Avago Broadcom Compatible
Transceiver SFP+ 32G Fibre Channel-SW (1310nm, SMF, 100m,
DOM, Ind Temp)

Brand : ATGBICS

Product code: FTLF8532P5BNV-C

Product name : FTLF8532P5BNV Avago Broadcom
Compatible Transceiver SFP+ 32G Fibre Channel-SW
(1310nm, SMF, 100m, DOM, Ind Temp)

FTLF8532P5BNV Finisar Compatible Transceiver SFP+ 32G Fibre Channel-SW (1310nm, SMF, 100m,
DOM, Ind Temp)

ATGBICS FTLF8532P5BNV Avago Broadcom Compatible Transceiver SFP+ 32G Fibre Channel-SW
(1310nm, SMF, 100m, DOM, Ind Temp):

ATGBICS FTLF8532P5BNV 32GBase-Fibre Channel supports a distance of up to 100m over single-mode
fibre (SMF) using a wavelength of 1310nm via an LC connector. Digital optical monitoring (DOM) support
is also present enabling real-time monitoring of the parameters of the fibre optic transceiver. Our
product meets the specification of Finisar FTLF8532P5BNV= and we proudly offer a compatibility
guarantee and lifetime warranty. Our rigorously tested products record a unique traceable serial number
and are fully compliant with all MSA Standards.

Performance		Features	
SFP transceiver type *	Fiber optic	Certification	CE, FCC, RoHS
Maximum data transfer rate *	28050 Mbit/s	Power	
Interface type *	SFP28	Input voltage	3.3 V
Single-mode fiber (SMF) supported	✓	Maximum voltage	3.5 V
Multi-mode fiber (MMF) supported	✗	Power consumption (typical)	1 W
Fiber optic connector	LC	Operational conditions	
SFP transceiver standard	SW	Maximum operating temperature	85 °C
Maximum transfer distance	100 m	Operating temperature (T-T)	0 - 85 °C
Wavelength	1310 nm	Storage temperature (T-T)	-40 - 85 °C
Ethernet LAN	✓	Operating relative humidity (H-H)	0 - 95%
Ethernet interface type	32 Gigabit Ethernet	Storage relative humidity (H-H)	0 - 95%
Digital Diagnostics Monitoring (DDM)	✓	Weight & dimensions	
Wavelength-division multiplexing (WDM)	✗	Width	13.4 mm
Features		Depth	56.5 mm
Product colour	Silver	Height	8.5 mm
Housing material	Metal	Weight	20 g
Plug and Play	✓	Packaging data	
Hot-Plug support	✓	Number of products included	1 pc(s)
Hot-swap	✓	Package type	Box
Easy to install	✓	Technical details	
Country of origin	China	Sustainability compliance	✓
Brand compatibility	Finisar	Sustainability certificates	RoHS
		Doesn't contain	Lead





5056468771087

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 26-JAN-2024. Prints or copies of Information are only valid on the printed Publication date