

Data sheet

2789.0 H 150,0/54 YE



Wire-end ferrules, Max. wire cross-section: 150 mm², Length: 54 mm, Length of copper pipe: 32 mm, Colour: Yellow

RAL: 1026

Business data

Article number	2789.0
Article name	H 150,0/54 YE
GTIN (EAN)	4044211055189
Packaging unit	25
Quantity unit	PC
Weight per piece (not including packaging)	11.18 g
Weight per piece (including packaging)	11.32 g
Unit of weight	G
Customs number	85369010
Country of origin	DE
Product description	Ferrules
Colour	Yellow

Technical data

Dimensions

Length	54 mm
Length of copper pipe	32 mm
Diameter of copper pipe	18.5 mm
Diameter plastic collar	23.5 mm
Wall thickness of copper pipe	0.5 mm
Wall thickness of plastic collar	0.75 mm

Connection data

Wire cross-section, max.	150 mm ²
Wire cross-section AWG, max.	250 kcmil
Stripping length	38 mm

Materials

Copper pipe	Copper alloy
Surface	Galvanically tin-plated, shiny
Plastic collar	Polypropylene homopolymer
Working temperature, min.	-5 °C
Working temperature, max.	105 °C

Further technical data

Insulation available	✓
----------------------	---

Environmental Product Compliance

REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes

Approvals

Standards and regulations

DIN 46228-4:1990	yes
------------------	-----

Media

Accessories
