



Crimp lug, Pin shape acc. to DIN 46231, Length: 24 mm, Max. wire cross-section: 2.5 mm², Colour: Blue

RAL: Ähnlich 5005

Business data

Article number	2546.0
Article name	SKS 2,5
GTIN (EAN)	4044211053390
Connector shape	Pen shape acc. to DIN 46231
Product-compliant (according to DIN)	yes
Packaging unit	100
Quantity unit	PC
Weight per piece (not including packaging)	0.82 g
Weight per piece (including packaging)	0.83 g
Unit of weight	G
Customs number	85369010
Country of origin	TW
Product description	Crimp
Colour	Blue

Technical data

Dimensions

Length	24 mm
Length of pin	10.5 mm
Width of pin	1.9 mm
Diameter of feed-in funnel	4.5 mm
Size DIN	2.5

Connection data

Wire cross-section, min.	1.5 mm ²
Wire cross-section, max.	2.5 mm ²
Wire cross-section AWG, min.	16
Wire cross-section AWG, max.	14

Materials

Connector material	Copper
Surface	Tin-plated
insul.	Expanded PA insulation
Working temperature, min.	-55 °C
Working temperature, max.	105 °C

Further technical data

Insulation available	✓
Soldered	✓

Environmental Product Compliance

REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes

Approvals

Standards and regulations

Standards / specifications	DIN EN 13599
----------------------------	--------------

Media

Accessories
