

ATGBICS FWLF-1519-7D-53 Finisar Compatible Transceiver CWDM SFP 1000Base (1531nm, SMF, LC, DOM)

Brand : ATGBICS

Product code: FWLF-1519-7D-53-C

Product name : FWLF-1519-7D-53 Finisar Compatible Transceiver CWDM SFP 1000Base (1531nm, SMF, LC, DOM)



FWLF-1519-7D-53 Finisar Compatible Transceiver CWDM SFP 1000Base (1531nm, SMF, LC, DOM)
ATGBICS FWLF-1519-7D-53 Finisar Compatible Transceiver CWDM SFP 1000Base (1531nm, SMF, LC, DOM). SFP transceiver type: Fiber optic, Maximum data transfer rate: 1000 Mbit/s, Interface type: SFP. Product colour: Silver, Housing material: Metal, Country of origin: United Kingdom. Input voltage: 3.3 V, Maximum voltage: 3.5 V, Power consumption (typical): 1 W. Width: 13.4 mm, Depth: 56.5 mm, Height: 8.5 mm. Number of products included: 1 pc(s), Package type: Box



Performance		Power	
SFP transceiver type *	Fiber optic	Input voltage	3.3 V
Maximum data transfer rate *	1000 Mbit/s	Maximum voltage	3.5 V
Interface type *	SFP	Power consumption (typical)	1 W
Single-mode fiber (SMF) supported	✓	Operational conditions	
Multi-mode fiber (MMF) supported	✗	Maximum operating temperature	70 °C
Fiber optic connector	LC	Operating temperature (T-T)	0 - 70 °C
SFP transceiver standard	CWDM	Storage temperature (T-T)	-40 - 85 °C
Wavelength	1531 nm	Operating relative humidity (H-H)	0 - 95%
Coarse Wavelength Division Multiplexing (CWDM)	✓	Storage relative humidity (H-H)	0 - 95%
Ethernet LAN	✓	Weight & dimensions	
Ethernet interface type	Gigabit Ethernet	Width	13.4 mm
Digital Diagnostics Monitoring (DDM)	✓	Depth	56.5 mm
		Height	8.5 mm
		Weight	20 g
Features		Packaging data	
Product colour	Silver	Number of products included	1 pc(s)
Housing material	Metal	Package type	Box
Plug and Play	✓	Technical details	
Hot-swap	✓	Sustainability compliance	✓
Easy to install	✓	Sustainability certificates	RoHS
Country of origin	United Kingdom	Doesn't contain	Lead
Brand compatibility	Finisar		
Certification	CE, FCC, RoHS		



5056468767639

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 26-JAN-2024. Prints or copies of Information are only valid on the printed Publication date