

Data sheet

2802.0 HZL/16,0-D BU



Wire-end ferrules, Max. wire cross-section: 16 mm², Length: 29 mm, Length of copper pipe: 16 mm, Colour: Blue

RAL: Ähnlich 5005

Business data

Article number	2802.0
Article name	HZL/16,0-D BU
GTIN (EAN)	4044211055318
Packaging unit	50
Quantity unit	PC
Weight per piece (not including packaging)	1.39 g
Weight per piece (including packaging)	1.4 g
Unit of weight	G
Customs number	85369010
Country of origin	DE
Product description	Ferrules
Colour	Blue

Technical data

Dimensions

Length	29 mm
Length of copper pipe	16 mm
Width of plastic collar	9.5 mm
Height of plastic collar	17.2 mm
Diameter of copper pipe	8.3 mm
Wall thickness of copper pipe	0.3 mm
Wall thickness of plastic collar	0.6 mm

Connection data

Wire cross-section, max.	16 mm ²
Wire cross-section AWG, max.	6
Stripping length	20 mm
2-wire plastic collar	✓

Materials

Copper pipe	Copper alloy
Surface	Galvanically tin-plated, shiny
Plastic collar	Polypropylene homopolymer
Working temperature, min.	-5 °C
Working temperature, max.	105 °C

Further technical data

Insulation available	✓
----------------------	---

Environmental Product Compliance

REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes

Data sheet

2802.0 HZL/16,0-D BU



Approvals

Standards and regulations

DIN 46228-4:1990	yes
------------------	-----

Media

Accessories
