# 3M<sup>TM</sup> Mini D Ribbon (MDR) Connectors

## .050" IDC Wiremount Plug - Shielded



- Wiper-on-wiper contact for reliable repetitive plugging
- MDR digital LCD interface as a 20 or 26 contact connector
- IEEE 1284C Interface as a 36 contact connector
- Accepts a wide variety of cable constructions including flat, round, twisted pair and twinax cables
- Accepts a wide variety of shielded junction shells
- Contacts: 14, 20, 26, 36, 40, 50, 68, 80 and 100
- RoHS Compliant. See the Regulatory Information Appendix (RIA) in the "RoHS compliance" section of www.3Mconnector.com for compliance information (RIA E1 & C1 apply)

Date Modified: July 19, 2010

TS-0423-B Sheet 1 of 3

## **Physical**

Insulation Material:	Glass Reinforced Polyester
Flammability:	UL 94V-0
Body Color:	Black
Cover Color:	Black, Gray
Contact:	
Material:	Beryllium Copper
Underplating:	80 μ" [2.0 μm] Nickel
Wiping Area Plating:	30 μ" [0.76 μm] Min. Gold
IDC Contacts Plating:	Gold flash
Shroud:	
Material:	Steel
Plating:	Nickel
Wire Accommodation:	
Black Cover:	28 AWG Stranded, 30 AWG Solid (Insulation Diameter = 0.7 mm Max.)
Gray Cover:	26 AWG Solid (Insulation Diameter = $0.7 \text{ mm}$ to $0.9 \text{ mm}$ )
Marking:	3M Logo and Part Number

## Electrical

Current Rating: 1A

**Insulation Resistance:**  $>1 \times 10^8 \Omega$  at 500 V<sub>DC</sub>

Withstanding Voltage: 500 V<sub>RMS</sub> for 1 Minute

## Environmental

**Temperature Rating:** -20°C to +85°C

UL File No.: E68080

## $3M^{\text{TM}}$ Mini D Ribbon (MDR) Connectors

.050" IDC Wiremount Plug - Shielded

101 Series



### ЗМ

Electronic Solutions Division Interconnect Solutions http://www.3Mconnector.com 3M is a trademark of 3M Company. For technical, sales or ordering information call 800-225-5373

# $3M^{\text{TM}}$ Mini D Ribbon (MDR) Connectors

### .050" IDC Wiremount Plug - Shielded



1 = Gray Cover: 26 AWG Solid (Available in 68 Contact Only)

### 3M is a trademark of 3M Company. For technical, sales or ordering information call 800-225-5373

TS-0423-B Sheet 3 of 3

Electronic Solutions Division Interconnect Solutions http://www.3Mconnector.com

ЗМ

#### **Important Notice**

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

#### Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for a period of one (1) year from the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.



**3M Electronics Solutions Division** 6801 River Place Blvd. Austin, TX 78726-9000 U.S.A. 1-800-225-5373 www.3Mconnector.com

Please recycle. Printed in USA. © 3M 2010. All rights reserved. RIA-2217B-E