



Pushing Performance
Since 1945

Han3A RJ45 Cat5 coupler 8p plastic



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 225 1107
Specification	Han3A RJ45 Cat5 coupler 8p plastic
HARTING eCatalogue	https://b2b.harting.com/09452251107

Identification

Category	Connectors
Series	RJ45
Element	Double coupling
Specification	incl. installation frame metal

Version

Size	Han [®] 3 A
Shielding	Fully shielded, 360° shielding contact
Number of contacts	8

Technical characteristics

Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
Limiting temperature	-40 ... +70 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65
	IP67

Material properties

Material (hood/housing)	Polycarbonate (PC)
Colour (hood/housing)	Black



Pushing Performance
Since 1945

Material properties

Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Antimony trioxide
	Lead
	Nickel
	Naphthalene

Specifications and approvals

Approvals	DNV GL
PROFINET	Yes

Commercial data

Packaging size	1
Net weight	84 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140059788
ETIM	EC001264
eCl@ss	27440190 Industry connector (unspecified)