



Pushing Performance  
Since 1945

# Han 3A RJ45 HYBRID PLUG AC



Image is for illustration purposes only. Please refer to product description.

Part number	09 57 308 0500 000
Specification	Han 3A RJ45 HYBRID PLUG AC
HARTING eCatalogue	<a href="https://b2b.harting.com/09573080500000">https://b2b.harting.com/09573080500000</a>

## Identification

Category	Connectors
Series	RJ45 Hybrid
Element	Cable connector
Specification	Straight
Type of hood/housing	Hood

## Version

Size	Han® 3 A
Shielding	Fully shielded, 360° shielding contact
Number of contacts	8
Contact configuration	L1, PE, N
further contacts	+ 3x 300 V AC

## Technical characteristics

Conductor cross-section	0.08 ... 0.22 mm² Stranded
Conductor cross-section	AWG 28 ... AWG 24 Stranded
Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
Limiting temperature	-40 ... +70 °C



**Pushing Performance**  
Since 1945

## Material properties

RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Antimony trioxide Lead Nickel
Requirement set with Hazard Levels	R26

## Specifications and approvals

Approvals	DNV GL
-----------	--------

## Commercial data

Packaging size	10
Net weight	153 g
Country of origin	Germany
European customs tariff number	85367000
GTIN	5713140072510
ETIM	EC002636
eCl@ss	27440113 Rectangular connectors (set)