

## DSUB HD MA RA 26P S4 4-40 NUT AND B-LOCK



Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Connectors
Series	D-Sub
Identification	High Density
Element	Connector
Description of the contact	Stamped Angled

### Version

Termination method	Wave soldering termination
Gender	Male
Size	D-Sub 2
Number of contacts	26
PCB fixing	With board locks
Locking type	Fixing flange with thread 4-40 UNC

### Technical characteristics

Distance between rows	1.98 mm
Contact spacing (termination side)	2.29 mm
Rated current	2 A
Clearance distance	$\geq 1$ mm
Creepage distance	$\geq 1$ mm
Insulation resistance	$> 5 \times 10^9$ $\Omega$
Contact resistance	<25 m $\Omega$

## Technical characteristics

Tightening torque	≤0.6 Nm Female screw lock
Limiting temperature	-40 ... +85 °C
Performance level	NM 30 (S4) 1
Mating cycles	≥500
Test voltage U <sub>r.m.s.</sub>	1 kV
Isolation group	IIIa (175 ≤ CTI < 400)
PCB thickness	1.6 mm
Installation height	6.3 mm
Hot plugging	No

## Material properties

Material (insert)	Thermoplastic resin, glass-fibre filled (PBTP) Shell: steel, nickel plated
Colour (insert)	Black
Material (contacts)	Copper alloy
Surface (contacts)	Noble metal over Ni Mating side Sn over Ni Termination side
Layer thickness	≥0.76 µm
Layer thickness	≥30 µinch
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	ecef7555-f643-4ceb-a337-fc54762297f1
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Requirement set with Hazard Levels	R26

## Specifications and approvals

Specifications	DIN 41652
----------------	-----------

## Commercial data

Packaging size	100
Net weight	11.873 g
Country of origin	China
European customs tariff number	85366990
GTIN	5713140071636
ETIM	EC001136
eCl@ss	27440214 D-Sub coupler