Lighting Controls

Preset Slide Dimmer

DATE:	LOCATION:
TYPE:	PROJECT:
CATALOG #:	

FEATURES

- Compatible with 0-10V LED drivers and fluorescent and HID ballasts
- No power pack required for controlling 0–10V drivers or ballasts
- Linear slider for superior quality and dimming performance
- Separate ON/OFF switch and dim slider to preserve preset light level
- · Can be used in single-pole or 3-way applications
- · Compatible with decorator-style wall plates
- Fits easily into a standard wallbox and is suitable for multi-gang installations
- · Trim adjustment for fine tuning





SPECIFICATIONS

ELECTRICAL

- Standard ON/OFF
- Frequency: 60Hz
- Voltage: 120/277VAC
- · Load Rating: 10A @120VAC, 5A @277VAC
- Load Type: 0-10V (120/277V), 0-10V Fluorescent (120V), 0-10V Fluorescent (277V)
- Switch Type: SIngle-Pole & 3-Way
- 0-10V Control

MOUNTING

- · Single-gang NEMA-style switch box (standard wall switch box)
- · Decorator-style wall plate sold separately

· Available in White, Ivory, and Light Almond

CERTIFICATIONS

· cULus, UL 1472, Title 24, NEMA SSL 7A

WARRANTY

1 year warranty

OPERATING ENVIRONMENT

• Operating Temperature: 0°C to 40°C (32°F to 104°F)

ORDERING GUIDE

CATALOG #

Model

PSD0108-UNV Preset Slide Dimmer for 0–10V LED drivers and fluorescent and HID ballasts, Single Pole or 3-Way, 10A@120VAC, 5A@277VAC

Color WH White IV Ivory LA Light Almond

Example: PSD0108-UNV-WH





Lighting Controls

Preset Slide Dimmer

DATE:	LOCATION:
TYPE:	PROJECT:

DIMENSIONS







WIRING DIAGRAMS

SINGLE LOCATION CONTROL

CATALOG #:



TWO LOCATION CONTROL



Pink wire replaces previous gray wire. Units with a gray instead of pink wire should be wired as the pink wire shown in the diagram.

