



## Description

It is critical for household goods, electronic toys, consumer electronics and security controls to be built with long lasting, high quality parts that can be counted on to work every time. The RB series rolling ball sensor switches from C&K feature an ultraminiature design and are available with several different angle options to trigger, helping ensure they fit any product.

### **Features & Benefits**

- Different angle options to trigger
- Ultra miniature design

# Applications

- Consumer electronics including irons, portable heaters, games, toys
- Safety and security controls
- Household goods
- Electronic toys

Patent awarded

## **RB-231X2 Information**

Specifications				
Contact Arrangement	SPST			
Sensor Angle	0° to -10° scope inside, terminal to disconnection electric current			
Electrical Characteristics				
Maximum Voltage	5 VDC 1mA (resistive load)			
Minimum Voltage	1 VDC 10mA (resistive load)			

	Materials
Frame	Copper alloy, nickel plated
Cover	PA 46 (UL94V-0)
Movable Contact	Copper alloy, nickel plated
Terminals	Copper alloy, gold plated
Brass Ball	Brass, gold plated

#### **Ordering Number**

Operating Life Insulation Resistance

Dielectric Strength Operating Temperature

Part number list is shown below. For individual part details, please refer to the following.

100,000 cycles

1,000 M Ω min. @ 100 VDC 500 V AC (50-60 Hz)

-20°C to 70°C

		<u>ø 5</u>	4.2 12.4
Part Number (Part Description)	Product Details		
RB-231X2	Rolling Ball Sensor Switch	T XL	
Part Number	Packaging	6.1	
RB-231X2	1,000 pieces		0.27
			0.7
		2.5	4.8 SOTO
		ø1 <del>4.8</del>	
			OPEN 10°
		PCB LAYOUT	



Insulation Resistance

Dielectric Strength Operating Temperature



# **RB-220-07A Information**

Specifications			
Contact Arrangement	SPST		
Sensor Angle	In the range of 15° to 90°, current appears between terminals		
Electrical Characteristics			
Maximum Voltage	5 VDC 1mA (resistive load)		
Minimum Voltage	1 VDC 10µA (resistive load)		
Operating Life	100,000 cycles		

10 M Ω min. @ 100 VDC

100 V AC (50-60 Hz)

-10°C to 50°C

	Materials	
Cover	PA	
Housing	r <del>A</del>	
Silicon Sheet	Silica	
Terminals	Copper alloy, gold plated	
Brass Ball	Brass, gold plated	

Part Number (Part Description)	Product Details
RB-220-07A R	Rolling Ball Sensor Switch
Part Number	Packaging
RB-220-07A R	500 pieces



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littlefuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at <a href="http://www.littlefuse.com/disclaimer-electronics">http://www.littlefuse.com/disclaimer-electronics</a>.

