



RoHS


REV	ECN NO.	DESRPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2023.11.25



*MATERIAL (IDC)
INSULATOR:PBT (UL 94V-0)
Contact:Copper Alloy.
Contact Plated:Gold or Tin over Nickel Plated.
*SPECIFICATIONS
TEMPERATURE RANGE:-20°C TO-105° C
CONTACT RESISTANCE:3Ω MAX.
TNSULATION RESISTANCE:5MΩ MIN.
WITHSTANDING VOLTAGE:300V 10S



序号	名称	规格描述	数量
①	插头	IDC-30P 1.27mm	2
②	电线	UL2678 30AWG 0.635间距灰排 7/0.10TS	30P
③	卡扣	一个凸点朝外，一个凸点朝内同向30P（1.27mm）	2

X.±0.50	X.°±	PART NO: CL1272230100BQ10E	XFCN 兴飞连接器					
.X±0.25	.X°±							
.XX±0.15	.xx°±							
.XXX±0.10	.xxx°±							
UNITS:	mm	TITLE: 灰排线两端IDC1.27/30P L=100mm 不含插头	0769-82001899					
			www.xfconn.com					
			DWG NO: /					
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN		APPD			VIEW			
		CHKD						
		DRAW	Wang		SCALE	SHEET	REV	
		DATE	2023.11.25		NONE	1:1	A1	