



RoHS

REV	ECN NO.	DESRPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2023.11.25



*MATERIAL (IDC)
INSULATOR:PBT (UL 94V-0)
Contact:Copper Alloy.
Contact Plated:Gold or Tin over Nickel Plated.
*SPECIFICATIONS
TEMPERATURE RANGE:-20°C TO-105° C
CONTACT RESISTANCE:3Ω MAX.
TNSULATION RESISTANCE:5MΩ MIN.
WITHSTANDING VOLTAGE:300V 10S



序号	名称	规格描述	数量
①	插头	IDC-40P 1.27mm	2
②	电线	UL2678 30AWG 0.635间距灰排 7/0.10TS	40P
③	卡扣	一个凸点朝外，一个凸点朝内同向40P（1.27mm）	2

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN	X.±0.50	X.°±	PART NO: CL1272240100BQ10E	XFCN 兴飞连接器		
	.X±0.25	.X°±				
	.XX±0.15	.xx°±				
	.XXX±0.10	.xxx°±		0769-82001899		
	UNITS:	mm		www.xfconn.com		
			TITLE: 灰排线两端IDC1.27/40P L=100mm 不含插头	DWG NO: /		
			APPD	VIEW		
			CHKD			
			DRAW	Wang	SCALE	SHEET
			DATE	2023.11.25	NONE	1:1
						REV
						A1