



RoHS

REV	ECN NO.	DESRPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2023.11.25



*MATERIAL (IDC)
INSULATOR:PBT (UL 94V-0)
Contact:Copper Alloy.
Contact Plated:Gold or Tin over Nickel Plated.
*SPECIFICATIONS
TEMPERATURE RANGE:-20°C TO-105° C
CONTACT RESISTANCE:3Ω MAX.
TNSULATION RESISTANCE:5MΩ MIN.
WITHSTANDING VOLTAGE:300V 10S



序号	名称	规格描述	数量
①	插头	IDC-50P 1.27mm	2
②	电线	UL2678 30AWG 0.635间距灰排 7/0.10TS	50P
③	卡扣	一个凸点朝外, 一个凸点朝内同向50P (1.27mm)	2

X.±0.50	X.°±	PART NO: CL1272250100BQ10E	XFCN 兴飞连接器			
.X±0.25	.X°±					
.XX±0.15	.xx°±					
.XXX±0.10	.xxx°±					
UNITS:	mm					
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN		TITLE: 灰排线两端IDC1.27/50P L=100mm 不含插头	0769-82001899			
			www.xfconn.com			
			DWG NO: /			
		APPD		VIEW		
		CHKD				
DRAW	Wang	SCALE	SHEET	REV		
DATE	2023.11.25	NONE	1:1	A1		