



RoHS


| REV | ECN NO. | DESRPTION | DESIGN | APPROVAL | DATE       |
|-----|---------|-----------|--------|----------|------------|
| A1  | NEW     | 更换图框      |        |          | 2023.11.25 |



\*MATERIAL (IDC)  
INSULATOR:PBT (UL 94V-0)  
Contact:Copper Alloy.  
Contact Plated:Gold or Tin over Nickel Plated.  
\*SPECIFICATIONS  
TEMPERATURE RANGE:-20°C TO-105° C  
CONTACT RESISTANCE:3Ω MAX.  
TNSULATION RESISTANCE:5MΩ MIN.  
WITHSTANDING VOLTAGE:300V 10S



| 序号 | 名称 | 规格描述                            | 数量  |
|----|----|---------------------------------|-----|
| ①  | 插头 | IDC-34P 1.27mm                  | 2   |
| ②  | 电线 | UL2678 30AWG 0.635间距灰排 7/0.10TS | 34P |
| ③  | 卡扣 | 一个凸点朝外，一个凸点朝内同向34P (1.27mm)     | 2   |

|                                                                                                                                                                |        |                               |                                            |                                                                                                       |       |     |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------|--------|-------------------------------|--------------------------------------------|-------------------------------------------------------------------------------------------------------|-------|-----|
| X.±0.50                                                                                                                                                        | X.°±   | PART NO:<br>CL1272234100BQ10E | <b>XFCN</b> 兴飞连接器                          |                                                                                                       |       |     |
| .X±0.25                                                                                                                                                        | .X°±   |                               |                                            |                                                                                                       |       |     |
| .XX±0.15                                                                                                                                                       | .xx°±  |                               | TITLE:<br>灰排线两端IDC1.27/34P<br>L=100mm 不含插头 | 0769-82001899                                                                                         |       |     |
| .XXX±0.10                                                                                                                                                      | .xxx°± |                               |                                            | www.xfconn.com                                                                                        |       |     |
| UNITS:                                                                                                                                                         | mm     |                               | DWG NO: /                                  |                                                                                                       |       |     |
| THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN |        | APPD                          |                                            | VIEW <div></div> |       |     |
|                                                                                                                                                                |        | CHKD                          |                                            |                                                                                                       |       |     |
|                                                                                                                                                                |        | DRAW                          | Wang                                       | SCALE                                                                                                 | SHEET | REV |
|                                                                                                                                                                |        | DATE                          | 2023.11.25                                 | NONE                                                                                                  | 1:1   | A1  |
|                                                                                                                                                                |        |                               |                                            |                                                                                                       |       |     |