



RoHS


REV	ECN NO.	DESRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2023.11.25



*MATERIAL (IDC)
INSULATOR:PBT (UL 94V-0)
Contact:Copper Alloy.
Contact Plated:Gold or Tin over Nickel Plated.
*SPECIFICATIONS
TEMPERATURE RANGE:-20°C TO-105° C
CONTACT RESISTANCE:3Ω MAX.
TNSULATION RESISTANCE:5MΩ MIN.
WITHSTANDING VOLTAGE:300V 10S



序号	名称	规格描述	数量
①	插头	IDC-26P 三件式 (2.0mm)	2
②	电线	UL2651 28AWG 1.0间距灰排 7/0.127TS	26P
③	卡扣	一个凸点朝外, 一个凸点朝内同向26P (2.0mm)	2

X.±0.50	X.°±	PART NO: CL2002326100BC10E	XFCN 兴飞连接器			
.X±0.25	.X°±					
.XX±0.15	.xx°±		TITLE: 灰排线两端IDC2.0/26P 三件式 L=100mm 不含插头	0769-82001899		
.XXX±0.10	.xxx°±			www.xfconn.com		
UNITS:	mm		DWG NO: /			
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED,COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN		APPD		VIEW 		
		CHKD				
		DRAW	Wang	SCALE	SHEET	REV
		DATE	2023.11.25	NONE	1:1	A1