



RoHS

REV	ECN NO.	DESRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2023.11.25

*MATERIAL (IDC)
INSULATOR:PBT (UL 94V-0)
Contact:Copper Alloy.
Contact Plated:Gold or Tin over Nickel Plated.
*SPECIFICATIONS
TEMPERATURE RANGE:-20°C TO-105° C
CONTACT RESISTANCE:3Ω MAX.
TNSULATION RESISTANCE:5MΩ MIN.
WITHSTANDING VOLTAGE:300V 10S



序号	名称	规格描述	数量
①	插头	IDC-12P 1.27mm	2
②	电线	UL2678 30AWG 0.635间距灰排 7/0.10TS	12P
③	卡扣	一个凸点朝外，一个凸点朝内同向12P（1.27mm）	2

X.±0.50	X.°±	PART NO: CL1272212100BQ10E	XFCN 兴飞连接器			
.X±0.25	.X°±					
.XX±0.15	.xx°±					
.XXX±0.10	.xxx°±					
UNITS:	mm	TITLE: 灰排线两端IDC1.27/12P L=100mm 不含插头	0769-82001899			
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED,COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN			www.xfconn.com			
			DWG NO: /			
		APPD				
		CHKD			VIEW	
		DRAW	Wang	SCALE	SHEET	REV
		DATE	2023.11.25	NONE	1:1	A1