



RoHS

REV	ECN NO.	DESRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2023.11.25



*MATERIAL (IDC)
INSULATOR:PBT (UL 94V-0)
Contact:Copper Alloy.
Contact Plated:Gold or Tin over Nickel Plated.
*SPECIFICATIONS
TEMPERATURE RANGE:-20°C TO-105° C
CONTACT RESISTANCE:3Ω MAX.
TNSULATION RESISTANCE:5MΩ MIN.
WITHSTANDING VOLTAGE:300V 10S



序号	名称	规格描述	数量
①	插头	IDC-30P 三件式 (2.0mm)	2
②	电线	UL2651 28AWG 1.0间距灰排 7/0.127TS	30P
③	卡扣	一个凸点朝外, 一个凸点朝内同向30P (2.0mm)	2

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN	X.±0.50	X.°±	PART NO: CL2002330100BC10E	XFCN 兴飞连接器				
	.X±0.25	.X°±						
	.XX±0.15	.xx°±						
	.XXX±0.10	.xxx°±						
	UNITS:	mm	TITLE: 灰排线两端IDC2.0/30P 三件式 L=100mm 不含插头		DWG NO: /			
			APPD		VIEW 			
			CHKD					
			DRAW	Wang	SCALE	SHEET	REV	
			DATE	2023.11.25	NONE	1:1	A1	