



Switches > Tactile Switches



Actuator Style: **Round**
Operating Function: **NO**
Contact Base Material: **Stainless Steel**
Switch Contact Plating Material: **Silver**
Low Profile: **Yes**

Features

Product Type Features

Switch Connection Type	Printed Circuit Board
Leg Style	J Style
Illuminated	Without
Actuator Style	Round

Configuration Features

ESD Grounding Terminal	With
Ganged	Without
Switch Feedback Type	Tactile
Operating Function	NO
Configuration (Pole-Throw)	Single Pole - Single Throw
Number of Actuators	Single

Electrical Characteristics

Operating Voltage	12 VDC
-------------------	--------

Body Features

--	--



Cover Material	Nickel, Silver
Actuator Force	260 g[9.17 oz]
Case Material	Thermoplastic
Actuator Profile	Extended
Actuator Material	Thermoplastic
Case Color	Black
Product Orientation	Vertical
Actuator Color	White

Contact Features

Contact Base Material	Stainless Steel
Switch Contact Plating Material	Silver
Contact Current Rating	50 mA

Termination Features

Termination Method to Printed Circuit Board	Surface Mount
---	---------------

Housing Features

Low Profile	Yes
Process Sealed	No

Dimensions

Product Height	2 mm[.079 in]
----------------	---------------

Usage Conditions

Operating Temperature Range	-25 – 70 °C
-----------------------------	-------------

Packaging Features

Packaging Method	Tape & Reel
------------------	-------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235)



	Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 2337234-1
TACT MICRO JB 4.6X4.4X0.55 P3.5
100GF




TE Part # 2337234-2
TACT MICRO JB 4.6X4.4X0.55 P3.5
160GF



TE Part # 2337234-3
TACT MICRO JB 4.6X4.4X0.55 P3.5
200GF



TE Part # 2337224-1
TACT ULTRA TB 2.6X1.6X0.55 160GF



TE Part # 2337225-1
TACT ULTRA TB 2.8X1.9X0.6 160GF

Also in the Series | [Alcoswitch LPT](#)



Tactile Switches(52)

Customers Also Bought



TE Part #1-1415899-7
RZ03-1A4-D024




TE Part #5745182-2
09 PLUG SP/MS STD




TE Part #3-1625892-1
3W SM M/OX 5% 220R



TE Part #4-1625892-1
3W SM M/OX 5% 330R




TE Part #1776244-4
4P TB ,90deg, VT, 5mm, Blue,w /interlock



TE Part #282836-3
TERM-BLOK PCB MOUNT 90 3P.



TE Part #1614959-9
CPF0805 1M2 0.1% 25PPM 1K RL



TE Part #2314844-8
8P,2MM,B-B,REC,DRVT,SMD,0.1AU, TB,W/CP



TE Part #ASDD006-09SN-HE
RECEPTACLE ASSEMBLY ASL 9-WAY



TE Part #1-1747981-4
Std HDMI, RA, SMT, Panel grd, Flange

Documents

Product Drawings

TACT MINI JB 5.2X5.2X2 260GF

English

CAD Files

Customer View Model

ENG_CVM_CVM_2337245-4_B.3d_igs.zip

English

Customer View Model



[ENG_CVM_CVM_2337245-4_B.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2337245-4_B.2d_dxf.zip](#)

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

MSLPT Family-Low-profile Tactile Switches

English