

3.5Ø 4P PHONE JACK PLUG



SPECIFICATIONS:

1. ELECTRICAL CHARACTERISTICS

- 1-1. RATING: 20V, 1A Min.
- 1-2. CONTACT RESISTANCE:
 - 50 MILLIOHMS MX. FOR INITIAL,
 - 80 MILLIOHMS Mqx. AFTER 5000 CYCLES
- 1-3. INSULATION RESISTANCE: 100 MEGAOHMS Min BY SOOV DC AFTER 1 MINUTE.
- 1-4. DIELECTRIC WITHSTANDING VOLTAGE: 500V RMS AFTER 1 MINUTE

2. MECHANICAL CHARACTERISTICS

- 2-1. INSERTION FORCE: 0.3~3.0 KGF/2.94~29.4NI
- 2-2. WITHDRAWAL FORCE: 0.3~3.0 KGF 2.94~29.4NI
- 3. LIFE TEST: 5,000 CYCLES MIN.



No.	PART NAME	QTY	MATERIAL (THICK)	PLATING (COLOR)
①	MYLAR	1	N/A	AMBER
②	HOUSING	1	HIGH TEMP. THERMOPLASTIC	Black
③	LOOP	1	COPPER ALLOY	Au-Plated
④	TERMINAL 6#	1	COPPER ALLOY t=0.20	Au-Plated
⑤	TERMINAL 5#	1	COPPER ALLOY t=0.20	Au-Plated
⑥	TERMINAL 4#	1	COPPER ALLOY t=0.20	Ni-Plated
⑦	TERMINAL 3#	1	COPPER ALLOY t=0.25	Ni-Plated
⑧	TERMINAL 2#	1	COPPER ALLOY t=0.20	Au-Plated
⑨	TERMINAL 1#	1	COPPER ALLOY t=0.20	Au-Plated

广东星坤科技股份有限公司

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
Δx					ANGULAR ±5°
Δx					L ≤ 4 ±0.2
Δx					4 < L ≤ 16 ±0.3
Δx					16 < L ≤ 63 ±0.4
Δx					L > 63 ±0.5



DSND		SCALE: N/A	MODEL TYPE: 3.5 PHONE JACK
DWN		VIEW:	PART NO.:
CHKD		UNIT: mm/in	DWG NO.: PJ-3565D
APPD		SIZE: A4	WEIGHT
			SHEET 1/1
			REVISIT A0

文件工程章