

[Home](#) > [5611002090F](#)

Search For  Part Number

Part Number: **5611002090F**

General Description	
Color	Blue
Series	561
Configuration	5 mm Lens
Description	5 mm Stand -Off 0.900" WC Blue
Package Options	Bulk Packaging
Sizes	5mm
Lamp Type	Single Color
Viewing	Top View
Polarity	Cathode Right
Lens Style	Non -Diffused

Absolute Maximum Ratings (Ta = 25Å °)	
Derating	from 40Å° @ .5 mA/Å°C
Solder Temperature	260Å° for 5 sec
Operating Temperature	-30 to +85
Storage Temperature	-40 to +100

Operating Characteristics	
Color	Blue
LED Type	High Efficiency
Luminous Intensity Min	0.9
Luminous Intensity Typical	1.5
Test Current mA	20mA
Emitted Color	Blue
Power Dissipation Max	120mW



5611002090F

[check stock](#)



[This is a  
RoHS Compliant Product  
To learn more click here](#)