





Contact Rating:	50mA, 12V DC
Contact Resistance:	100mΩ max
Insulation Resistance:	100mΩ min. 500V DC
Dielectric Strength:	250V AC/1minute
Travel:	0.25mm
Operating Temp:	-20℃~+80℃
Storage Temp:	-20℃~+80℃



PAPT NO	TS-1102SD-X-X-X
Operating Force	A:100gf B:160gf C:260gf
Height	Code-x
Color	B:Black BR:Brown R:Red O:Orange Y:Yellow BL:Blue W:White

⑤	Terminal	—	4	Brass (0.30t)	Plating silvering	—
④	Contact	—	1	F.ag/Sus	Natural	—
③	Base	—	1	Pa46		—
②	Cover	—	1	Spcc	Plating Nickel	—
①	Keystake	—	1	Pa46		—
ITEM	PAPT NAME	TER.NO	QTY	MATERIAL	FINISHING	REMARK

东生洋行科技股份有限公司						ANGLAR	±5°
ΔX		日期				L ≤ 4	±0.2
ΔX						4 < L ≤ 16	±0.3
ΔX						16 < L ≤ 63	±0.4
MARK		DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5
亨 件 工 程 章						UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-da.cn							

	DSND		SCALE: N/A	MODEL TYPE: TACT SWITCH		
	DWN		VIEW: 	PART NO.: TS-1102SD-X-X-X		
	CHKD		UNIT: mm/in	DWG NO.:		
	APPD		SIZE: A4			
XKB INDUSTRIAL PRECISION CO., LIMITED				WEIGHT	SHEET	REVISI
					1/1	A0