





Contact Rating:	50mA,12V DC
Contact Resistance:	100MΩ max
Insulation Resistance:	100MΩ min.500V DC
Dielectric Strength:	250V AC/1minute
Travel:	0.25mm
Operating Temp:	-30℃~+85℃
Storage Temp:	-30℃~+80℃

Code-x	H
A	4.3
B	4.5
C	5.0
D	5.5
E	6.0
F	6.5
G	7.0
H	7.5
I	8.0
J	8.5
K	9.0
L	9.5
M	10.0
N	10.5

Code-x	H
O	11.0
P	11.5
Q	12
R	12.5
S	13.0
T	13.5
U	14.0
V	15.0
W	15.5
X	16
Y	16.5
Z	17
18	18
19	19

PAPT NO	TC-1102-X-X-X
Operating Force	A:100gf B:160gfC:260gf
Height	Code-x
color	B:Black BR:Brown R:Red O:Orange Y:Yellow BL:Blue W:White

⑤	Terminal	—	4	Brass (0.30t)	Plating silvering	—
④	Contact	—	1	F.ag/Sus	Natural	—
③	Base	—	1	Pa46		—
②	Cover	—	1	Spcc	Plating Nickel	—
①	Keystake	—	1	Pa46		—
ITEM	PAPT NAMF	TER,NO	QTY	MATERIAL	FINISHING	REMARK

广东星坤科技股份有限公司										DSND		SCALE: N/A		MODEL TYPE: TACT SWITCH	
										DWN		VIEW: 		PART NO.: TC-1102-X-X-X	
										CHKD		UNIT: mm/in		DWG NO.:	
										APPD		SIZE: A4			
ΔX Δx Δx MARK 日期 DESCRIPTION DATE REVISED APPROVED										ANGLAR ±5° L≤ 4 ±0.2 4<L≤ 16 ±0.3 16<L≤ 63 ±0.4 L> 63 ±0.5					
文件工程章										UNSPECIFIED TOLERANCES		XKB INDUSTRIAL PRECISION CO.,LIMITED		WEIGHT	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn														SHEET 1/1	
														REVISIC A0	